



Recommended Xerox Media for Xerox DocuColor 8002/7002

Revision:1.0 August 2008

1st Revision

This supersedes any previous Recommended Media for Xerox DocuColor 8002 / 7002

Important Note:

Media recommendations made in this publication are based on qualification tests conducted using standard test images with moderate to heavy image area coverage.

Test machines are maintained within specifications defined by user documentation.

* Testing environment Temperature 23 degreesC±2, Relative Humidity 50% ±5. Relative Humidity range 20-50%.

Reliability is based on your operating environment and application mix.

Machine reliability specifications may be affected by high usage of heavy weight and specialty stocks.

In addition, variances in machine reliability may occur due to extended use of some media types.

© 2009 Xerox Corporation. All rights reserved.

Xerox®, the sphere of connectivity design, and all Xerox product names and product numbers mentioned in this publication are trademarks of Xerox Corporation. Other company trademarks are also acknowledged.

Warranty disclaimer:

Xerox makes no guarantees or warranties, either expressed or implied, concerning the performance, use or replacement of non-Xerox branded media or throughput products.

Customers should inquire directly of their paper distributor or manufacturer for any guidance when purchasing a particular media product for the first time, customers are advised to purchase small quantities to insure that their expectations are met.

The quality of Xerox supplies is consistent from ream to ream and is backed by a 100% guarantee.

The quality of non-Xerox branded paper may vary from ream to ream or carton to carton, so for optimum performance on Xerox Colour equipment, use only the best - Xerox supplies.

EUROPEAN RECOMMENDED MATERIALS LIST- DocuColor 8002/7002

Weight Range Specification Instructions for Printing one side (Simplex) or two sides (Duplex)	Decurler Setting paper type	Standard Cut Sizes				Grammage Weight (g/m ²) Weight of the paper in grams per square meter	DC8002/7002 Trays/ Weight Selection and Best Practices for Operation											
		A4 210x297 mm	A3 297x420 mm	A3+ 305x457 mm	SRA3 320x450 mm		60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-220 gsm		221-300 gsm	
		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4			IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4					
						Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	
Xerox Digital Colour Impressions 80 gsm	A	3R97661	3R97662		80	OK All Trays	OK All Trays											
				3R97991	90			OK All Trays	OK All Trays									
Xerox Digital Colour Colotech + Gold 90 gsm	A		3R97990		90			OK All Trays	OK All Trays									
		3R97988			90			OK All Trays	OK All Trays									
Xerox Digital Colour Colotech + 90 gsm	A		3R94642		90			OK All Trays	OK All Trays									
		3R94641	3R94643		90			OK All Trays	OK All Trays									
				3R95838	90			OK All Trays	OK All Trays									
Xerox Digital Colour Impressions 90 gsm	A		3R97664		90			OK All Trays	OK All Trays									
		3R97663			90			OK All Trays	OK All Trays									
Xerox Digital Colour Colotech + Gold 100 gsm	A		3R97955		100			OK All Trays	OK All Trays									
		3R97993			100			OK All Trays	OK All Trays									
Xerox Digital Colour Colotech + 100 gsm	A		3R94647		100			OK All Trays	OK All Trays									
		3R94646	3R94648		100			OK All Trays	OK All Trays									
Xerox Digital Colour Colotech Natural White 100 gsm	A		3R97103		100			OK All Trays	OK All Trays									
		3R97102			100			OK All Trays	OK All Trays									
Xerox Digital Colour Impressions 100 gsm	A		3R97667		100			OK All Trays	OK All Trays									
		3R97666			100			OK All Trays	OK All Trays									
Xerox Digital Colour Colotech+ Gold 120 gsm	B		3R97959		120					OK All Trays	OK All Trays							
		3R97958			120			OK All Trays	OK All Trays									
Xerox Digital Colour Colotech+ 120 gsm	B		3R94652		120			OK All Trays	OK All Trays									
		3R94651	3R94653		120			OK All Trays	OK All Trays									
Xerox Digital Colour Impressions 120 gsm	A		3R97669		120			OK All Trays	OK All Trays									
		3R98685			120			OK All Trays	OK All Trays									
Uncoated Heavy Stocks	Decurler Setting paper type																	
Xerox Digital Colour Impressions 160 gsm	A		3R98008		160					Tray 3 & 4	Tray 3 & 4							
		3R98007			160			OK All Trays	OK All Trays	OK All Trays	OK All Trays							
Xerox Digital Colour Colotech + Gold 160 gsm	A		3R97964		160			OK All Trays	OK All Trays									
		3R97963			160			OK All Trays	OK All Trays									
Xerox Digital Colour Colotech + 160 gsm	A		3R94657		160			OK All Trays	OK All Trays									
		3R94656	3R94658		160			OK All Trays	OK All Trays									
Xerox Digital Colour Colotech Natural White 160 gsm	A		3R95957		160			OK All Trays	OK All Trays									
		3R95956			160			OK All Trays	OK All Trays									
Xerox Digital Colour Colotech + Gold 200 gsm	A		3R97968		200							OK All Trays	OK All Trays					
		3R97967			200			OK All Trays	OK All Trays			OK All Trays	OK All Trays					
Xerox Digital Colour Colotech + 200 gsm	A		3R94662		200			OK All Trays	OK All Trays			OK All Trays	OK All Trays					
		3R94661			200			OK All Trays	OK All Trays			OK All Trays	OK All Trays					
Xerox Digital Colour Colotech Natural White 200 gsm	A		3R95959		200			OK All Trays	OK All Trays			OK All Trays	OK All Trays					
		3R95958			200			OK All Trays	OK All Trays			OK All Trays	OK All Trays					

EUROPEAN RECOMMENDED MATERIALS LIST- DocuColor 8002/7002

	Standard Cut Sizes	Grammage Weight (g/m2)	DC8002/7002 Trays/ Weight Selection and Best Practices for Operation																			
			A4 210x297 mm		A3 297x420 mm		A3+ 305x457 mm		SRA3 320x450 mm		60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-220 gsm		221-300 gsm	
			IOT: Trays 1 and 2 SFM: Trays 3 and 4	IOT: Trays 1 and 2 SFM: Trays 3 and 4	IOT: Trays 1 and 2 SFM: Trays 3 and 4	IOT: Trays 1 and 2 SFM: Trays 3 and 4	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex
Weight Range Specification																						
Instructions for Printing one side (Simplex) or two sides (Duplex)																						
Super Gloss Coated Heavy Stocks C15	Deculer Setting paper type																					
		Select 106-135 gsm mode. Load with coated side up.																				
Xerox Digital Colour Colotech + SuperGloss 135	A	3R97679																				
Image quality will not be as good on second side																						
		Select 187-220 gsm mode. Load with coated side up.																				
Xerox Digital Colour Colotech + SuperGloss 160	A	3R97681																				
Image quality will not be as good on second side																						
Xerox Digital Colour Colotech + SuperGloss 210	A	3R97680																				
Image quality will not be as good on second side (not recommended for rated speed)																						
		3R97682	3R97683																			
Xerox Digital Colour Colotech + SuperGloss 250	A				3R97684																	
Image quality will not be as good on second side (not recommended for rated speed)																						
		3R97687			3R97688																	
		3R97686																				
Specialties	Deculer Setting paper type																					
Xerox Digital Colour Colotech Super 210 A4 Prescored White	A	Second side image quality will not be as good as side one																				
Xerox DocuCard 500 sheet box	A	3R97685																				
Xerox DocuGlossCard 500 sheet box	A	3R97571																				
Xerox ValuPeelCard Coated 500 sheet box	A	3R97678																				
Xerox ValuPeelCard Uncoated 500 sheet box	A	3R97953																				
Xerox ValuPerfCard Coated 500 sheet box	A	3R97952																				
Xerox ValuPerfCard Uncoated 500 sheet box	A	3R97677																				
Xerox Premium Never Tear	Default	3R98056	3R98057		3R98031																	
Select Coated 136-186 g/m2 Transfer +130. Each batch run should not be more than 500 duplex. Must run 50 sheets paper between batches. Static in sheets may cause issues.																						
Select Coated 136-186 g/m2 Transfer +150. Each batch run should not be more than 500 duplex. Must run 50 sheets paper between batches. Static in sheets may cause issues.																						
		3R98058	3R98059		3R98035																	
Specialties																						
Xerox DuraPaper X250	A	Select Uncoated 187-220 gsm mode. Load image side up.																				
Xerox DocuPac Glossy White Presentation folder	A	3R97513																				
Xerox DocuPac Matt Presentation folder	A	3R97251																				
Xerox Colotech Supergloss Document Folder (not recommended for rated speed)	A	3R97353																				
Xerox Laser Business Cards 10-UP	A	3R97634																				
Xerox Laser Window GraphiX Clear (window decal)	A	3R97512																				
Xerox Laser Window GraphiX Opaque White (window decal)	A	3R97511																				
		3R97539																				

* Custom Paper Profiles (BIB) adjustment may be required to achieve optimum image quality

EUROPEAN RECOMMENDED MATERIALS LIST- DocuColor 8002/7002

		Standard Cut Sizes				Grammage Weight (g/m2) Weight of the paper in grams per square meter	DC8002/7002 Trays/ Weight Selection and Best Practices for Operation												
		A4	A3	A3+	SRA3		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4				
		210x297 mm	297x420 mm	305x457 mm	320x450 mm		60-80 gsm		81-105 gsm		106-135 gsm		136-166 gsm		187-220 gsm		221-300 gsm		
Weight Range Specification						Simplex		Duplex		Simplex		Duplex		Simplex		Duplex			
Instructions for Printing one side (Simplex) or two sides (Duplex)						Simplex		Duplex		Simplex		Duplex		Simplex		Duplex			
Transfer oaper		Select coated 136-186 gsm mode - image side up. Each batch run should not exceed 500 sheets. 100 sheets Colotech Paper should be run between batches. No more than 500 sheets per day																	
Xerox Transfer paper	A	3R97949															OK All Trays		
Tab Stock	Decurler Setting paper type	Feed Long Edge First, Tabs Trailing																OK All Trays	
Xerox Digital Colour Colotech Tabs * Xerox Digital Colour Colotech Tabs* white	B	3R97231				200												OK All Trays	
Xerox Mylar Tabs* White 100 X 5 reverse	B	3R97232																OK All Trays	
Transparencies (not recommended for rated speed)	Decurler Setting paper type	3R97229				200												OK All Trays	
Xerox Universal Transparency with paper backing (200 SHEET BOX)	Default	FOR HIGH PRINT QUALITY Select Uncoated 221-300 gsm mode. Load transparency facing up.																	
Xerox Universal Transparency with paper backing SRA3	Default	3R98199			3R98201	100 micron												OK All Trays	
Xerox Universal Transparency with paper backing (200 SHEET BOX)	Default	FOR HIGH SPEED (STANDARD PRINT QUALITY) Select Uncoated 187-220 gsm mode. Load transparency facing up.																	
Xerox Universal Transparency with paper backing SRA3	Default	3R98199			3R98201	100 micron												OK All Trays	
Label Stock	Decurler Setting paper type	Label Stock (Approximately)																	
Xerox Colour Laser Printer Labels																			
1 PER A4	C	3R93872				190												OK All Trays	
6 PER A4		3R93873				190												OK All Trays	
8 PER A4		3R93874					190											OK All Trays	
14 PER A4		3R93875					190											OK All Trays	
24 PER A4		3R97524					190												OK All Trays
Xerox laser Colour Gloss Coated Labels																			
1 PER A4	C	3R97288				190												OK All Trays	
2 to view CD labels	C	3R97287				190												OK All Trays	
Xerox CD Colotech + Matt label & CD insert Combi Box	C&A	3R97515				190 & 120												OK All Trays	
Xerox Durapaper Label (polyolefin face material)	C	3R97344	3R98645		3R98688	250												OK All Trays	
Xerox Glossy White Self Adhesive Label A4 (not recommended for rated speed)	Default	Select Uncoated 221-280 gsm mode. Load image side up.																	
		3R97245				190													OK All Trays
Xerox Glossy White Self Adhesive Label SRA3 (recommended for rated speed)					3R97348	190													OK All Trays
Xerox Crystal Clear Adhesive Label A4 (not recommended for rated speed)		3R97244				190													OK All Trays
Xerox Crystal Clear Adhesive Label SRA3 (recommended for rated speed)				3R97347	190													OK All Trays	
Xerox Colobind Gloss Covers	Decurler Setting paper type	Limit Tray capacity to 50 sheets. Image quality can vary from good to fair depending on score quality. Slightly degraded image quality on uncoated side. Image coated side 1st to minimize gloss/oil streaking. Do not image within 6mm around the score lines. Manual duplex printing only. Post Script custom size required for 6mm, 9mm and 12 mm spines																	
Spine width 1.5 mm		3R98022				210												OK All Trays Manual Duplex	
Spine width 3 mm		3R98023				210												OK All Trays Manual Duplex	
Spine width 6 mm		3R98024				210												OK All Trays Manual Duplex	
Spine width 9 mm		3R98025				210												OK All Trays Manual Duplex	
Spine width 12 mm		3R98026				210												OK All Trays Manual Duplex	