



Recommended Xerox Media for Xerox DocuColor 5000AP

Revision: 1.0 June 2008

Last revision Aug 2007

Important Note:

Media recommendations made in this publication are based on qualification tests conducted using standard test images with moderate to heavy image area coverage.

Test machines are maintained within specifications defined by user documentation.

* Testing environment Temperature 23 degreesC±2, Relative Humidity 50 % ±5. Relative Humidity range 20-50 %.

Reliability is based on your operating environment and application mix.

Machine reliability specifications may be affected by high usage of heavy weight and specialty stocks. In addition, variances in machine reliability may occur due to extended use of some media types.

© 2006 Xerox Corporation. All rights reserved.

Xerox®, The Document Company®, the stylized X®, and all Xerox product names and product names and product numbers mentioned in this publication are trademarks of Xerox Corporation.

Other company trademarks are also acknowledged.

Warranty disclaimer:

Xerox makes no guarantees or warranties, either expressed or implied, concerning the performance, use or replacement of non-Xerox branded media or throughput products.

Customers should inquire directly of their paper distributor or manufacturer for any guidance when purchasing a particular media product for the first time, customers are advised to purchase small quantities to insure that their expectations are met.

The quality of Xerox supplies is consistent from ream to ream and is backed by a 100 % guarantee.

The quality of non-Xerox branded paper may vary from ream to ream or carton to carton, so for optimum performance on Xerox Colour equipment, use only the best - Xerox supplies.



EUROPEAN RECOMMENDED MATERIALS LIST- DocuColor 5000AP

Weight Range Specification Instructions for Printing one side (Simplex) or two sides (Duplex) and laser grades)	Decurler Setting paper type	Standard Cut Sizes				Grammage Weight (g/m2) Weight of the paper in grams per square meter	DC5000AP Trays/ Weight Selection and Best Practices for Operation									
		A4 210x297 mm	A3 297x420 mm	A3+ 305x457 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4	
		60-80 gsm		81-105 gsm			106-135 gsm		136-166 gsm		167-300 gsm					
						Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	
Xerox Digital Colour Impressions 80 gsm	A	3R97661	3R97662			80	OK All Trays	OK All Trays								
					3R97991	90	OK All Trays	OK All Trays								
Xerox Digital Colour Colotech + Gold 90 gsm	A		3R97990			90			OK All Trays	OK All Trays						
		3R97988				90			OK All Trays	OK All Trays						
					3R95838	90			OK All Trays	OK All Trays						
Xerox Digital Colour Colotech + 90 gsm	A		3R94642			90			OK All Trays	OK All Trays						
					3R94643	90			OK All Trays	OK All Trays						
		3R94641				90			OK All Trays	OK All Trays						
Xerox Digital Colour Impressions 90 gsm	A		3R97664			90			OK All Trays	OK All Trays						
		3R97663				90			OK All Trays	OK All Trays						
					3R97956	100			OK All Trays	OK All Trays						
Xerox Digital Colour Colotech + Gold 100 gsm	A		3R97955			100			OK All Trays	OK All Trays						
						100			OK All Trays	OK All Trays						
		3R97993				100			OK All Trays	OK All Trays						
					3R95839	100			OK All Trays	OK All Trays						
Xerox Digital Colour Colotech + 100 gsm	A		3R94647			100			OK All Trays	OK All Trays						
					3R94648	100			OK All Trays	OK All Trays						
		3R94646				100			OK All Trays	OK All Trays						
Xerox Digital Colour Colotech Natural White 100 gsm	A		3R97103			100			OK All Trays	OK All Trays						
		3R97102				100			OK All Trays	OK All Trays						
					3R97668	100			OK All Trays	OK All Trays						
Xerox Digital Colour Impressions 100 gsm	A		3R97667			100			OK All Trays	OK All Trays						
		3R97666				100			OK All Trays	OK All Trays						
Xerox Digital Colour Colotech+ Gold 120 gsm	B		3R97959			120					OK All Trays	OK All Trays				
						120					OK All Trays	OK All Trays				
		3R97958				120					OK All Trays	OK All Trays				
					3R95840	120					OK All Trays	OK All Trays				
Xerox Digital Colour Colotech+ 120 gsm	B		3R94652			120					OK All Trays	OK All Trays				
					3R94653	120					OK All Trays	OK All Trays				
		3R94651				120					OK All Trays	OK All Trays				
Xerox Digital Colour Impressions 120 gsm	A	3R98685				120					OK All Trays	OK All Trays				
			3R97669			120					OK All Trays	OK All Trays				
Uncoated Heavy Stocks	Decurler Setting paper type															
Xerox Digital Colour Impressions 160 gsm	A		3R98008		3R98686	160							Tray 3 & 4	Tray 3 & 4		
						160							OK All Trays	OK All Trays		
		3R98007				160							OK All Trays	OK All Trays		
					3R97965	160							OK All Trays	OK All Trays		
Xerox Digital Colour Colotech + Gold 160 gsm	A		3R97964			160							OK All Trays	OK All Trays		
						160							OK All Trays	OK All Trays		
		3R97963				160							OK All Trays	OK All Trays		
Xerox Digital Colour Colotech + 160 gsm	A		3R94657		3R95841	160							OK All Trays	OK All Trays		
						160							OK All Trays	OK All Trays		
		3R94656				160							OK All Trays	OK All Trays		
					3R97276	160							OK All Trays	OK All Trays		
Xerox Digital Colour Colotech Natural White 160 gsm	A		3R95957			160							OK All Trays	OK All Trays		
						160							OK All Trays	OK All Trays		
		3R95956				160							OK All Trays	OK All Trays		
					3R97969	200							OK All Trays	OK All Trays		
Xerox Digital Colour Colotech + Gold 200 gsm	A		3R97968			200							OK All Trays	OK All Trays		
						200							OK All Trays	OK All Trays		
		3R97967				200							OK All Trays	OK All Trays		
Xerox Digital Colour Colotech + 200 gsm	A		3R94662		3R95842	200							OK All Trays	OK All Trays		
						200							OK All Trays	OK All Trays		
		3R94661				200							OK All Trays	OK All Trays		
Xerox Digital Colour Colotech Natural White 200 gsm	A		3R95959		3R97277	200							OK All Trays	OK All Trays		
						200							OK All Trays	OK All Trays		
		3R95958				200							OK All Trays	OK All Trays		
					3R97973	220							OK All Trays	OK All Trays		
Xerox Digital Colour Colotech + Gold 220 gsm	A		3R97972			220							OK All Trays	OK All Trays		
						220							OK All Trays	OK All Trays		
		3R97971				220							OK All Trays	OK All Trays		
					3R95843	220							OK All Trays	OK All Trays		
Xerox Digital Colour Colotech + 220 gsm	A		3R94669			220							OK All Trays	OK All Trays		
					3R94670	220							OK All Trays	OK All Trays		
		3R94668				220							OK All Trays	OK All Trays		



EUROPEAN RECOMMENDED MATERIALS LIST- DocuColor 5000AP

Weight Range Specification	Decurler Setting paper type	Standard Cut Sizes				Grammage Weight (g/m2) Weight of the paper in grams per square meter	DC5000AP Trays/ Weight Selection and Best Practices for Operation																
		A4 210x297 mm	A3 297x420 mm	A3+ 305x457 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4								
		60-80 gsm		81-105 gsm			106-135 gsm		136-186 gsm		187-300 gsm												
Instructions for Printing one side (Simplex) or two sides (Duplex)												Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex
Super Gloss Coated Heavy Stocks	A	Select 106-135 gsm mode. Load with coated side up.				135																	
C15		3R97679																					
Xerox Digital Colour Colotech + SuperGloss 135 Image quality will not be as good on second side	A	Select 187-220 gsm mode. Load with coated side up.				160																	
Xerox Digital Colour Colotech + SuperGloss 160 Image quality will not be as good on second side	A	3R97680	3R97681			160																	
Xerox Digital Colour Colotech + SuperGloss 210 Image quality will not be as good on second side	A	3R97682	3R97683		3R97684	210																	
Xerox Digital Colour Colotech + SuperGloss 250 Image quality will not be as good on second side	A				3R97688	250																	
		3R97686	3R97687			250																	
		3R97686				250																	
Specialties	A	Second side image quality will not be as good as side one				Various																	
Xerox Digital Colour Colotech Super 210 A4 Prescored White		3R97685					160																
Xerox ValuPerfCard Coated 500 sheet box	A	3R97677	Maximum of 50 sheet stacks			216																	
Xerox ValuPerfCard Uncoated 500 sheet box	A	3R97690	Maximum of 50 sheet stacks			216																	
Xerox DuraPaper X250	A	Select Uncoated 221-300 gsm mode. Load image side up																					
					3R97513	250 microns																	
Xerox DocuPac Glossy White Presentation folder	A	Select Coated 187-220 gsm mode - load glossy side up, score line trailing				210																	
Xerox DocuPac Matt Presentation folder	A	Select uncoated 187-220 gsm mode - load glossy side up, score line trailing.				180																	
		3R97353	Image quality not as good as Colotech +																				
Xerox Laser Business Cards 10-UP	A	Select uncoated 187-220 gsm mode in Tray image side up.				195																	
		3R97512																					
Xerox Colotech Supergloss Document Folder	A	Select coated 221-300 gsm mode for glossy side, uncoated 221-300 gsm for matt side				250																	
					3R97634																		
Tab Stock	B	Select Uncoated 187-220 gsm mode. Load SEF				200																	
Xerox Digital Colour Colotech Tabs* white 100x5 reverse		3R97231																					
Xerox Digital Colour Colotech Tabs* white 50x10 reverse	B	3R97232				200																	
Xerox Mylar Tabs* White 100 X 5 reverse	B	3R97229				200																	
Xerox Mylar Tabs* White 50 X 10 reverse	B	3R97230				200																	

* Feed Long Edge First, Tabs Trailing



EUROPEAN RECOMMENDED MATERIALS LIST- DocuColor 5000AP

	Decurler Setting paper type	Standard Cut Sizes				Grammage Weight (g/m2) Weight of the paper in grams per square meter	DC5000AP Trays/ Weight Selection and Best Practices for Operation									
		A4 210x297 mm	A3 297x420 mm	A3+ 305x457 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4	
Weight Range Specification						60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-300 gsm		
Instructions for Printing one side (Simplex) or two sides (Duplex)						Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	
Transparencies																
FOR HIGH PRENT QUALITY Select Uncoated 221-300 gsm mode. Load transparency facing up.																
Xerox Universal Transparency with Paper backing (250 SHEET BOX)	Default					3R98199									OK All Trays	
Xerox Universal Transparency with Paper backing SRA3	Default					3R98201									OK All Trays	
FOR HIGH SPEED (STANDARD PRINT QUALITY) Select Uncoated 187-220 gsm mode. Load transparency facing up.																
Xerox Universal Transparency with Paper backing (250 SHEET BOX)	Default					3R98199									OK All Trays	
Xerox Universal Transparency with Paper backing SRA3	Default					3R98201									OK All Trays	
Label Stock																
Decurler Setting paper type						Label Stock (Approximately)										
Xerox Colour Laser Printer Labels																
1 PER A4	C					3R93872									OK All Trays	
6 PER A4		3R93873				190									OK All Trays	
8 PER A4		3R93874				190									OK All Trays	
14 PER A4		3R93875				190									OK All Trays	
24 PER A4		3R93524				190									OK All Trays	
Xerox laser Colour Gloss Coated Labels																
1 PER A4	C					3R97288									OK All Trays	
2 to view CD labels	C					3R97287									OK All Trays	
Xerox CD Colotech + Matt label & CD insert Combi Box	C&A					3R97515									OK All Trays	
Xerox Durapaper Label (polyolefin face material) 1 PER A4	C					3R97344									OK All Trays	
Xerox Glossy White Self Adhesive Label A4																
Default						Select Uncoated 187-220 gsm mode. Load image side up.										
Default						3R97245									OK All Trays	
Default						3R97348									OK All Trays	
Xerox Glossy White Self Adhesive Label SRA3																
Decurler Setting paper type						Fan must be disabled prior to use*										
Carbonless Paper																
Xerox Premium Digital Carbonless Paper																
CB Singles White	A					3R99069									OK All Trays	
CB Singles White (PLE)		3R99088				82									OK All Trays	
CB Singles White (PSE)		3R99089				82									OK All Trays	
CB Singles Yellow		3R99080				82									OK All Trays	
CB Singles Pink		3R99083				82									OK All Trays	
CB Singles Blue		3R99082				82									OK All Trays	
CB Singles Green		3R99081				82									OK All Trays	
CFB Singles White		3R99070				86									OK All Trays	
CFB Singles Yellow		3R99071				86									OK All Trays	
CFB Singles Yellow (PLE)		3R99091				86									OK All Trays	
CFB Singles Yellow (PSE)		3R99092				86									OK All Trays	
CFB Singles Pink		3R99074				86									OK All Trays	
CFB Singles Pink (PLE)		3R99093				86									OK All Trays	
CFB Singles Blue		3R99072				86									OK All Trays	
CFB Singles Green		3R99073				86									OK All Trays	
CF Singles White		3R99075				82									OK All Trays	
CF Singles White (PLE)		3R99090				82									OK All Trays	
CF Singles Yellow		3R99076				82									OK All Trays	
CF Singles Pink		3R99077				82									OK All Trays	
CF Singles Pink (PLE)		3R99094				82									OK All Trays	
CF Singles Blue		3R99078				82									OK All Trays	
CF Singles Green		3R99079				82									OK All Trays	
A4+ CF Singles Yellow		3R99639				82									OK All Trays	
A4+ CF Singles Pink		3R99638				82									OK All Trays	
A4+ CF Singles Blue		3R99644				82									OK All Trays	
CF Singles Tag Cream		3R99146				170									OK All Trays	
CF Singles Tag White		3R99147				170									OK All Trays	
A4+ CF Singles Tag Cream		3R99640				170									OK All Trays	
A4+ CF Singles Tag Pink		3R99641				170									OK All Trays	
2-Part White / Yellow		A					3R99105									OK All Trays
2-Part White (PLE) / Yellow							3R99133									OK All Trays
2-Part White (PSE) / Yellow							3R99084									OK All Trays
2-Part White / Pink							3R99085									OK All Trays
							3R99107									OK All Trays
3-Part Straight White / Yellow / Pink		A					3R99108									OK All Trays
3-Part Straight White (PLE) / Yellow (PLE) / Pink							3R99135									OK All Trays
3-Part Straight White (PSE) / Yellow (PSE) / Pink							3R99086									OK All Trays
3-Part Reverse Pink / Yellow / White							3R99109									OK All Trays
4-Part Straight White / Yellow / Pink / Blue							3R99111									OK All Trays
4-Part Reverse Blue / Pink / Yellow / White		A				3R99112									OK All Trays	

* Contact your local Service Representative and refer to System Administration Guide for details