

XEROX

Technology | Document Management | Consulting Services

Recommended Xerox Media for Xerox DocuColor 8000AP / 8000 / 7000

Revision:7.0 December 2007

last revision September 2007

This supersedes any previous Recommended Media for Xerox DocuColor 8000AP / 8000 / 7000 list.

Important Note:

Media recommendations made in this publication are based on qualification tests conducted using standard test images with moderate to heavy image area coverage.

Test machines are maintained within specifications defined by user documentation.

* Testing environment Temperature 23 degreesC±2, Relative Humidity 50% ±5. Relative Humidity range 20-50%.

Reliability is based on your operating environment and application mix.

Machine reliability specifications may be affected by high usage of heavy weight and specialty stocks.

In addition, variances in machine reliability may occur due to extended use of some media types.

© 2003 Xerox Corporation. All rights reserved.

Xerox®, The Document Company®, the stylized X®, and all Xerox product names and product names and product numbers mentioned in this publication are trademarks of Xerox Corporation.

Other company trademarks are also acknowledged.

Warranty disclaimer:

Xerox makes no guarantees or warranties, either expressed or implied, concerning the performance, use or replacement of non-Xerox branded media or throughput products.

Customers should inquire directly of their paper distributor or manufacturer for any guidance when purchasing a particular media product for the first time, customers are advised to purchase small quantities to insure that their expectations are met.

The quality of Xerox supplies is consistent from ream to ream and is backed by a 100% guarantee.

The quality of non-Xerox branded paper may vary from ream to ream or carton to carton, so for optimum performance on Xerox Colour equipment, use only the best - Xerox supplies.

EUROPEAN RECOMMENDED MATERIALS LIST- DocuColor 8000AP / 8000 / 7000AP / 7000

Weight Range Specification Instructions for Printing one side (Simplex) or two sides (Duplex) Business Papers (Bond, xerographic, and laser grades)	Decurler Setting paper type	Standard Cut Sizes				Grammage Weight (g/m ²) Weight of the paper in grams per square meter	DC8000AP / 8000 / 7000AP / 7000 Trays/ Weight Selection and Best Practices for Operation											
		A4 210x297 mm	A3 297x420 mm	A3+ 305x457 mm	SRA3 320x450 mm		60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-220 gsm		221-300 gsm	
		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4			IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4					
						Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex			
Xerox Digital Colour Impressions 80 gsm	A	3R97661	3R97662		3R97991	80	OK All Trays	OK All Trays										
Xerox Digital Colour Colotech + Gold 90 gsm	A		3R97990			90			OK All Trays	OK All Trays								
Xerox Digital Colour Colotech + 90 gsm	A		3R94642		3R95838	90			OK All Trays	OK All Trays								
Xerox Digital Colour Impressions 90 gsm	A		3R94643			90			OK All Trays	OK All Trays								
Xerox Digital Colour Colotech + Gold 100 gsm	A		3R97664		3R97665	90			OK All Trays	OK All Trays								
Xerox Digital Colour Colotech + 100 gsm	A		3R97663		3R97956	90			OK All Trays	OK All Trays								
Xerox Digital Colour Colotech Natural White 100 gsm	A		3R97955			100			OK All Trays	OK All Trays								
Xerox Digital Colour Colotech + 100 gsm	A		3R97993			100			OK All Trays	OK All Trays								
Xerox Digital Colour Colotech + 120 gsm	B		3R94647		3R95839	100			OK All Trays	OK All Trays								
Xerox Digital Colour Colotech + 120 gsm	B		3R94648			100			OK All Trays	OK All Trays								
Xerox Digital Colour Impressions 100 gsm	A		3R97102		3R97103	100			OK All Trays	OK All Trays								
Xerox Digital Colour Colotech + 120 gsm	B		3R97666		3R97667	100			OK All Trays	OK All Trays								
Xerox Digital Colour Impressions 120 gsm	A		3R97668			100			OK All Trays	OK All Trays								
Xerox Digital Colour Impressions 160 gsm	A		3R97666		3R97960	120			OK All Trays	OK All Trays								
Xerox Digital Colour Colotech + 160 gsm	A		3R97959			120			OK All Trays	OK All Trays								
Xerox Digital Colour Colotech + 160 gsm	A		3R97958			120			OK All Trays	OK All Trays								
Xerox Digital Colour Colotech + 160 gsm	A		3R94652		3R95840	120			OK All Trays	OK All Trays								
Xerox Digital Colour Colotech + 160 gsm	A		3R94651		3R94653	120			OK All Trays	OK All Trays								
Xerox Digital Colour Impressions 200 gsm	A		3R97669		3R97670	120			OK All Trays	OK All Trays								
Xerox Digital Colour Impressions 200 gsm	A		3R98685			120			OK All Trays	OK All Trays								
Xerox Digital Colour Impressions 160 gsm	A		3R98008		3R98686	160					Tray 3 & 4	Tray 3 & 4						
Xerox Digital Colour Colotech + Gold 160 gsm	A		3R98007			160					OK All Trays	OK All Trays						
Xerox Digital Colour Colotech + 160 gsm	A		3R97964		3R97965	160					OK All Trays	OK All Trays						
Xerox Digital Colour Colotech + 160 gsm	A		3R97963			160					OK All Trays	OK All Trays						
Xerox Digital Colour Colotech + 160 gsm	A		3R94657		3R95841	160					OK All Trays	OK All Trays						
Xerox Digital Colour Colotech + 160 gsm	A		3R94656		3R94658	160					OK All Trays	OK All Trays						
Xerox Digital Colour Colotech Natural White 160 gsm	A		3R95957		3R97276	160					OK All Trays	OK All Trays						
Xerox Digital Colour Colotech + Gold 200 gsm	A		3R95956			160					OK All Trays	OK All Trays						
Xerox Digital Colour Colotech + 200 gsm	A		3R97967		3R97968	200					OK All Trays	OK All Trays						
Xerox Digital Colour Colotech + 200 gsm	A		3R94661		3R95842	200					OK All Trays	OK All Trays						
Xerox Digital Colour Colotech Natural White 200 gsm	A		3R94662			200					OK All Trays	OK All Trays						
Xerox Digital Colour Colotech Natural White 200 gsm	A		3R95959		3R97277	200					OK All Trays	OK All Trays						
Xerox Digital Colour Colotech Natural White 200 gsm	A		3R95958			200					OK All Trays	OK All Trays						

EUROPEAN RECOMMENDED MATERIALS LIST- DocuColor 8000AP / 8000 / 7000AP / 7000

	Decurler Setting paper type	Standard Cut Sizes				Grammage Weight (g/m2) Weight of the paper in grams per square meter	DC8000AP / 8000 / 7000AP / 7000 Trays/ Weight Selection and Best Practices for Operation											
		A4 210x297 mm	A3 297x420 mm	A3+ 305x457 mm	SRA3 320x450 mm		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4		IOT: Trays 1 and 2 SFM: Trays 3 and 4			
		Weight Range Specification Instructions for Printing one side (Simplex) or two sides (Duplex)					60-80 gsm		81-105 gsm		106-135 gsm		136-186 gsm		187-220 gsm		221-300 gsm	
						Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex	Simplex	Duplex			
Super Gloss Coated Heavy Stocks																		
C1S																		
Xerox Digital Colour Colotech + SuperGloss 135 Image quality will not be as good on second side	A	Select 106-135 gsm mode. Load with coated side up. 3R97679				135							OK All Trays	OK All Trays				
Xerox Digital Colour Colotech + SuperGloss 160 Image quality will not be as good on second side	A	Select 187-220 gsm mode. Load with coated side up. 3R97680				160							OK All Trays	OK All Trays				
Xerox Digital Colour Colotech + SuperGloss 210 Image quality will not be as good on second side (not recommended for rated speed)		3R97683				210							OK All Trays	OK All Trays				
Xerox Digital Colour Colotech + SuperGloss 250 Image quality will not be as good on second side (not recommended for rated speed)	A	3R97684				210							OK All Trays	OK All Trays				
		3R97688				250							OK All Trays*	OK All Trays	OK All Trays			
		3R97687				250							OK All Trays*	OK All Trays	OK All Trays			
		3R97686				250							OK All Trays	OK All Trays	Manual Duplex			
Specialties						Various												
Xerox Digital Colour Colotech Super 210 A4 Prescored White	A	3R97685 Second side image quality will not be as good as side one				160							OK All Trays	OK All Trays				
Xerox DocuCard 500 sheet box	A	3R97571 Maximum of 50 sheet stacks				160							OK All Trays	OK All Trays				
Xerox DocuGlossCard 500 sheet box	A	3R97678 Maximum of 50 sheet stacks				120							OK All Trays	OK All Trays				
Xerox ValuPeelCard Coated 500 sheet box	A	3R97953 Maximum of 50 sheet stacks				216							OK All Trays	OK All Trays				
Xerox ValuPeelCard Uncoated 500 sheet box	A	3R97952 Maximum of 50 sheet stacks				216							OK All Trays	OK All Trays				
Xerox ValuPerfCard Coated 500 sheet box	A	3R97677 Maximum of 50 sheet stacks				216							OK All Trays	OK All Trays				
Xerox ValuPerfCard Uncoated 500 sheet box	A	3R97690 Maximum of 50 sheet stacks				216							OK All Trays	OK All Trays				
Xerox Premium Never Tear	Default	Select Coated 136-186 g/m2 Transfer ±130. Each batch run should not be more than 500 duplex. Must run 50 sheets paper between batches. Static in sheets may cause issues. 3R98056				95 microns									Tray 3 Only	Tray 3 Only		
		Select Coated 136-186 g/m2 Transfer ±150. Each batch run should not be more than 500 duplex. Must run 50 sheets paper between batches. Static in sheets may cause issues. 3R98058				120 microns												
Specialties						Various												
Xerox DuraPaper X250	A	Select Uncoated 187-220 gsm mode. Load image side up. 3R97513				250 microns							OK All Trays	Manual Duplex				
Xerox DocuPac Glossy White Presentation folder	A	Select Coated 151-220 gsm mode - load glossy side up, score line trailing. 3R97251				210							OK All Trays	OK All Trays				
Xerox DocuPac Matt Presentation folder	A	Select uncoated 187-220 gsm mode- load glossy side up, score line trailing. 3R97353				180							OK All Trays	OK All Trays				
Xerox Colotech Supergloss Document Folder (not recommended for rated speed)	A	Select coated 221-300 gsm mode for glossy side, uncoated 221-280 gsm for matt side. 3R97634				250									OK All Trays	Manual Duplex		
Xerox Laser Business Cards 10-UP	A	Select uncoated 187-220 gsm mode in Tray 3- image side up. 3R97512				195									Tray 3 Only	Manual Duplex		
Xerox Laser Window GraphiX Clear (window decal)	A	Select coated 187-220 gsm mode - image side up. 3R97494				125 micron							OK All Trays	OK All Trays				
Xerox Laser Window GraphiX Opaque White (window decal)	A	Select coated 187-220 gsm mode - image side up. 3R97511				125 micron							OK All Trays	OK All Trays				
		3R97539																
Xerox Transfer paper	A	Select coated 136-186 gsm mode - image side up. Each batch run should not exceed 500 sheets. 100 sheets Colotech Paper should be run between batches. No more than 500 sheets per day. 3R97949											OK All Trays					
Tab Stock		3R97951 * Feed Long Edge First, Tabs Trailing																
Xerox Digital Colour Colotech Tabs * white 100x5 reverse	B	Select Uncoated 187-220 gsm mode. Load SEF. 3R97231				200							OK All Trays	OK All Trays				
Xerox Digital Colour Colotech Tabs*	B	3R97232											OK All Trays	OK All Trays				
Xerox Mylar Tabs* White 100 X 5 reverse	B	3R97229				200							OK All Trays	OK All Trays				

* Custom Paper Profiles (BTP) adjustment may be required to achieve optimum image quality

